

Product sheet



SYNERGY™ LEGRAND

Synergy™ Authentic - shaver socket - Brushed Stainless Steel

REF. 833090 | EAN. 3414970665447

> [Visit e-catalogue](#)

Product characteristics

- Supply : 230V~ 50/60Hz Output : 230V~ or 120V~ - 20VA max
- Back box to be min. 45mm deep
- Conform to BS EN 61558
- Cover plate is square 146x86 mm, product thickness is 7mm (once is installed onto the wall).
- Monobloc complete product = ready-to-install product

Recommendation / Restriction

- Recommended inside use only

The product's benefits

Installation

- Screwless live and neutral terminals

Usage


- Ideal for Hotel, suitable for use European, British and Australian 2 pin plugs

Advantages

- Plate in austenitic stainless steel Non magnetic Grade 304L
- Made in UK
- Delivered with screws for flush & surface boxes in both plastic and metal boxes

Documentation

CATALOGUE PAGE & OTHERS

 [ex223001_0726.pdf](#) | PDF (0.1Mo)

Agreements & Certificates

 [OC / CB-FR_709925](#) | (0.54Mo)