

# Product sheet



SYNERGY™ LEGRAND

Synergy™ Authentic - shaver socket - Brushed Stainless Steel

REF. 833090 | EAN. 3414970665447

> [Visit e-catalogue](#)

## Product characteristics

- Supply : 230V~ 50/60Hz Output : 230V~ or 120V~ - 20VA max
- Back box to be min. 45mm deep
- Conform to BS EN 61558
- Cover plate is square 146x86 mm, product thickness is 7mm (once is installed onto the wall).
- Monobloc complete product = ready-to-install product

## Recommendation / Restriction

- Recommended inside use only

## The product's benefits

### Installation

- Screwless live and neutral terminals

### Usage


- Ideal for Hotel, suitable for use European, British and Australian 2 pin plugs

### Advantages

- Plate in austenitic stainless steel Non magnetic Grade 304L
- Made in UK
- Delivered with screws for flush & surface boxes in both plastic and metal boxes

## Documentation

### CATALOGUE PAGE & OTHERS

 ex223001\_0726.pdf | PDF (0.1Mo)

### Agreements & Certificates

 OC / CB-FR\_709925 | (0.54Mo)