

Product sheet



SYNERGY™ LEGRAND

Synergy™ Authentic - shaver socket - Glossy Gold

REF. 833490 | EAN. 3414970668769

> [Visit e-catalogue](#)

Product characteristics

- Supply : 230V~ 50/60Hz Output : 230V~ or 120V~ - 20VA max
- Back box to be min. 45mm deep
- Conform to BS EN 61558
- Cover plate is square 146x86 mm,product thickness is 7mm (once is installed onto the wall).
- Monobloc complete product = ready-to-install product

Recommendation / Restriction

- Recommended inside use only

The product's benefits

Installation

- Screwless live and neutral terminals

Usage

- Ideal for Hotel, suitable for use European, British and Australian 2 pin plugs

Advantages

- Plate in Stainless steel rust resistance
- Made in UK
- Delivered with screws for flush & surface boxes in both plastic and metal boxes

Documentation

CATALOGUE PAGE & OTHERS

 ex223001_0726.pdf | PDF (0.1Mo)

Agreements & Certificates

 OC / CB-FR_709925 | (0.54Mo)