

Product sheet



SYNERGY™ LEGRAND

Synergy™ Slek - 1 gang switched single pole socket outlet 15A - Brushed Stainless Steel

REF. 832089 | EAN. 3414970661128

> [Visit e-catalogue](#)

Product characteristics

- BRITISH STANDARD 15A 250V~
- Type M 2P+E three round pins socket conform to BS546
- Screwless cover plate is square 86x86 mm, product thickness is 4mm (once is installed onto the wall).
- Complete product, cover plates are clipped onto the mechanism itself.

Recommendation / Restriction

- Recommended inside use only

The product's benefits

Installation

- Strip length indicator avoids waste of wires. Terminal screws backed off ready to cabling

Advantages

- Plate and switch rocker in same metal: austenitic stainless steel Non magnetic Grade 304L
- Made in UK
- Delivered with screws for flush & surface boxes in both plastic and metal boxes

Documentation

TECHNICAL DOCUMENTATION



F02268EN-00.pdf | PDF (0.66Mo)

CATALOGUE PAGE & OTHERS



ex223001_0729.pdf | PDF (0.1Mo)