

Product sheet



SYNERGY™ LEGRAND

Synergy™ Sleek - 1 gang switched double pole BS socket outlet 13A - Brushed Stainless Steel

REF. 832060 | EAN. 3414970660909

> [Visit e-catalogue](#)

Product characteristics

- Switched 2P+E British Standard, 13A, 250V
- Conform to BS1363 - 2, ASTA Licence
- Screw type terminals for a secured & enhanced contacts
- Screwless cover plate is square 86x86 mm, product thickness is 4mm (once is installed onto the wall).
- Complete product, cover plates are clipped onto the mechanism itself.

Recommendation / Restriction

- Recommended inside use only

The product's benefits

Installation

- Strip length indicator avoids waste of wires. Captive terminal screws backed off ready to cabling

Usage

- Fitted with safety shutters to maximise child protection

Advantages

- Plate and switch rocker in same metal: austenitic stainless steel Non magnetic Grade 304L
- Made in UK
- Delivered with screws for flush & surface boxes in both plastic and metal boxes

Documentation

TECHNICAL DOCUMENTATION



F02264EN-00.pdf | PDF (0.7Mo)

Agreements & Certificates



ASTA-780 | (0.28Mo)



G-MARK-LVE/2020/000875 v1 | (1.18Mo)

CATALOGUE PAGE & OTHERS



ex223001_0729.pdf | PDF (0.1Mo)