

Product sheet



SYNERGY™ LEGRAND

Synergy™ Authentic - 1 gang unswitched US standard socket outlet 15A - Brushed Stainless Steel

REF. 833099 | EAN. 3414970760227

> [Visit e-catalogue](#)

Product characteristics

- US standard 15A 127V~
- 2P+E Type B socket
- Cover plate is square 86x86 mm, product thickness is 7mm (once is installed onto the wall).
- Monobloc complete product = ready-to-install product

Recommendation / Restriction

- Recommended inside use only

The product's benefits

Installation

- Strip length indicator avoids waste of wires. Terminal screws backed off ready to cabling

Advantages

- Plate in austenitic stainless steel Non magnetic Grade 304L
- Made in UK
- Delivered with screws for flush & surface boxes in both plastic and metal boxes

Documentation

CATALOGUE PAGE & OTHERS

 [ex223001_0725.pdf](#) | PDF (0.08Mo)