

Product sheet



SYNERGY™ LEGRAND

Synergy™ Sleek - 2 gang switched single pole BS socket outlet 13A + USB chargers Type A&C - Brushed Stainless Steel

REF. 832079 | EAN. 3414970950956

> [Visit e-catalogue](#)

Product characteristics

- 2X2P+E British Standard, 13A, 250V + 3A 15W USB chargers Type A and C
- Conform to BS1363 - 2 USB charger conform to IEC62368 and IEC62680
- Screw type terminals for a secured & enhanced contacts
- Screwless cover plate is square 86x146 mm, product thickness is 4mm (once is installed onto the wall).
- Complete product, cover plates are clipped onto the mechanism itself.

Recommendation / Restriction

- Recommended inside use only

The product's benefits

Installation

- Strip length indicator avoids waste of wires. Terminal screws backed off ready to cabling

Usage

- Two in One product : Power outlet, fitted with safety shutters to maximise child protection + Convenient charging of USB devices

Avantages

- Plate and switch rocker in same metal: austenitic stainless steel Non magnetic Grade 304L
- Made in UK
- Delivered with screws for flush & surface boxes in both plastic and metal boxes

Documentation

TECHNICAL DOCUMENTATION

 F02762EN-01.pdf | PDF (0.65Mo)

Agreements & Certificates

 OC / CB-SE-104641M1 | (0.09Mo)


 OC / CB-SE-104641 | (1.37Mo)

 G-MARK-0048-1400-V-1 | (6.95Mo)

 OC CEM / CB EMC-220300363SHA-V1 | (0.6Mo)

 OC / CB-SE-102292 | (0.09Mo)

CATALOGUE PAGE & OTHERS

 ex223001_0729.pdf | PDF (0.1Mo)



OC / CB-SE-88178M1 | (0.87Mo)