

# Product sheet



MPX<sup>3</sup> LEGRAND

Motor protection circuit breaker MPX3 32S 6-10A  
50KA

REF. 417310 | EAN. 3414970395238

> [Visit e-catalogue](#)

## Product characteristics

- For the protection of 3 - ph motors 4kW / 415V
- Icu = 50kA / 415V Ics = 38kA / 415V
- Screw terminals capacity : 1mm<sup>2</sup> to 10mm<sup>2</sup> / 2 x 1mm<sup>2</sup> to 6mm<sup>2</sup>
- Compatible with MPX3 auxiliaries
- The device complies with substance-restriction requirements and has been designed in an environmentally conscious process.

## Recommendation / Restriction

- Product specially designed for tertiary and industrial installations. Recommended for the protection of 3-ph motors 4kW / 415V. Read the instructions before installing this product. Use only Legrand branded accessories.

## Documentation

### TECHNICAL DOCUMENTATION

- EXB19046\_TG\_3phase-asynchronous-motors\_EN.pdf | PDF (6.11Mo)
- LE07207AB.pdf | PDF (4.25Mo)
- F01988EN-05.pdf | PDF (2.86Mo)
- F01988FR-05.pdf | PDF (2.88Mo)

### CAD & Design specs / BIM

- 417300.dwg | DWG (0.15Mo)

## The product's benefits

### Installation

- Possible fixing on 35 mm "top hat" mounting rail (IEC 60715). Reduced size to optimize the space available in the cabinet.

### Usage

- Easy operation thanks to the rocker switch

### CATALOGUE PAGE & OTHERS

- ex223001\_0276-0277.pdf | PDF (0.69Mo)
- ex223001\_0274.pdf | PDF (0.04Mo)
- ex223001\_0272-0273.pdf | PDF (0.18Mo)
- ex223001\_0275.pdf | PDF (0.07Mo)
- ex223001\_0270.pdf | PDF (0.09Mo)

### Agreements & Certificates

- LGRP-00211-V01.01-EN.pdf | PDF (0.61Mo)