

Product sheet



CTX³ LEGRAND

Contactor CTX3 4P 135A 230V AC

REF. 416456 | EAN. 3414970403728

> [Visit e-catalogue](#)

Product characteristics

- Rating 135A (AC - 1) for switching resistive loads.
- Screw terminals capacity : Power 2 x 25mm² to 50mm² / Coil 0,75mm² to 2,5mm²
- Can be equipped with all Legrand CTX3 auxiliaries and Accessories .
- Endurance: up to 12 million mechanical operations and 1 million electrical operations. Number of operation cycles (AC-1) per hour : 1800.
- The device complies with substance-restriction requirements and has been designed in an environmentally conscious process.

Recommendation / Restriction

- Product specially designed for tertiary and industrial installations. Recommended for the switching of inductive and non-inductive loads. Read the instructions before installing this product. Use only Legrand branded accessories.

Documentation

TECHNICAL DOCUMENTATION

- LE07393AB.pdf | PDF (3.31Mo)
- F01991FR-04.pdf | PDF (3.19Mo)
- F01991EN-04 .pdf | PDF (3.12Mo)
- EXB19046_TG_3phase-asynchronous-motors_EN.pdf | PDF (6.11Mo)

CAD & Design specs / BIM

- 416446.dwg | DWG (0.2Mo)

The product's benefits

Installation

- Possible fixing on 35 mm "top hat" mounting rail (IEC 60715) and on mounting plate. Reduced size to optimize the space available in the cabinet.

Usage

- Engineered to allow easy coil replacement.

CATALOGUE PAGE & OTHERS

- ex223001_0294-0295.pdf | PDF (0.77Mo)
- ex223001_0292-0293.pdf | PDF (0.62Mo)
- ex223001_0285.pdf | PDF (0.12Mo)