

Product sheet



LEGRAND

Safety transformer - 230-400 V / 24-48 V - 1000 VA - 4 + 16 mm²

REF. 042726 | EAN. 3245060427269

> [Visit e-catalogue](#)

Product characteristics

- Transformers and auto-transformers IP 55 - class II - single-phase
- Safety transformers - Conform to standard IEC EN 61558 - 2 - 6 - For 63 VA transformers : - Fuse cartridges : 5 x 20 time - delayed - Fuse carrier : Cat.No 0 371 81 - For 100 VA and greater transformers : - Up to 25 A : gG 10 x 38 fuse cartridges and fuse carrier Cat. No. 0 058 08 - From 25 A to 50 A : gG 14 x 51 fuse cartridges and fuse carrier Cat.No 0 215 01 - From 50 A upwards : gG 22 x 58 fuse cartridges and fuse carrier Cat.No 0 216 01 - C curve MCBs Input voltage = 230 - 400 V~ Output voltage = 24 - 48 V~ - Power : 1000 VA - Primary terminal flexible cable : 4 mm² - Secondary terminal flexible cable cross - section : 16 mm²

Documentation

TECHNICAL DOCUMENTATION

 PRT219022-GT-transfosBT-BT-022020.pdf | PDF (4.27Mo)

CAD & Design specs / BIM

 042725.dwg | DWG (0.1Mo)

CATALOGUE PAGE & OTHERS

 ex223001_0504.pdf | PDF (0.04Mo)

 ex223001_0500.pdf | PDF (0.05Mo)

 ex223001_0502-0503.pdf | PDF (0.06Mo)

 ex223001_0496.pdf | PDF (0.06Mo)