

Product sheet



COLSON™ LEGRAND

Black cable tie Colson U.V. protected with internal teeth width 9mm and lenght 498 mm

REF. 031920 | EAN. 3414971132252

> [Visit e-catalogue](#)

Product charateristics

- The temporary zone (with arrows) allows the clamps to be put on hold before final tightening. The manual snap - in area allows the insertion effort to be reduced before final tightening on the mechanical area with the tool ref 031996.mécanique avec l'outil ref 031996.
- Tear - off performance. Conformity to EN 62275
- Ergonomic heads with soft curves for more comfort during handling. Single head
- Resistance to UV, chemical agents, temperature, -Max. temperature in permanent use 85 °C - Minimum temperature in permanent use (clamp installed)-40 °C - Minimum installation temperature-30 °C".

The product's benefits

Installation

- More comfort during installation.

Usage



- A packaging with a reinforced bottom and pre-cuts to access the collars on the front or top of the box. The belt clip system allows the box to be used on site as a handyman.

Avantages

- Ergonomics of Colson collars. 3 application zones patented by Legrand. Practical and ingenious packaging with several pre-cuts and a belt attachment system to make the collars easier to use during installation.
- Colson clamps are also available in grey for perfect adaptation to IRL type tubes.

Documentation

TECHNICAL DOCUMENTATION

-  F00139FR-10.pdf | PDF (1.16Mo)
-  F00139EN-10.pdf | PDF (1.16Mo)
-  F002529FR-00.pdf | PDF (0.45Mo)
-  F002529EN-00.pdf | PDF (0.44Mo)

Agreements & Certificates

-  LGRP-00673-V01.01-EN.pdf | PDF (0.56Mo)