

Product sheet



SYNERGY™ LEGRAND

Synergy™ Sleek - Double Pole switched Fused Connection Unit+blue LED power indicator - Brushed Stainless Steel

REF. 832035 | EAN. 3414970660640

> [Visit e-catalogue](#)

Product characteristics

- 13A, 250V~
- Screw type terminals for enhanced contacts accept wires up to 2X6mm²
- Marked terminals for easy identification
- Screwless cover plate is square 86x86 mm, product thickness is 4mm (once is installed onto the wall).
- Complete product, cover plates are clipped onto the mechanism itself.

Recommendation / Restriction

- Recommended inside use only

The product's benefits

Installation

- Compact mechanisms for maximum wiring space (back box to be min. 25mm) and slim front plates

Usage

- Oblong blue led to indicate the status of the connected device, which size is 11mm x 1,5mm, LED technology ensures the maximum quality in terms of reliability, efficiency, maintenance and energy saving
- No accessible electrical contact under the plate.

Avantages

- Plate and switch rocker in same metal: austenitic stainless steel Non magnetic Grade 304L
- Made in UK
- Delivered with screws for flush & surface boxes in both plastic and metal boxes

Documentation

TECHNICAL DOCUMENTATION

 F02657EN-00.pdf | PDF (0.15Mo)

Agreements & Certificates

 ASTA-880 | (0.24Mo)

CATALOGUE PAGE & OTHERS

 ex223001_0730.pdf | PDF (0.09Mo)