

Product sheet



SYNERGY™ LEGRAND

Synergy™ Sleek - Double Pole switched Fused Connection Unit+cord outlet+LED power indicator - Brushed Stainless Steel

REF. 832037 | EAN. 3414970660664

> [Visit e-catalogue](#)

Product characteristics

- 13A, 250V~
- Cord outlet allows the connection of an external device
- Screw type terminals for enhanced contacts accept wires up to 2X6mm²
- Screwless cover plate is square 86x86 mm, product thickness is 4mm (once is installed onto the wall).
- Complete product, cover plates are clipped onto the mechanism itself.

Recommendation / Restriction

- Recommended inside use only

The product's benefits

Installation

- Compact mechanisms for maximum wiring space (back box to be min. 25mm) and slim front plates

Usage

- Switch to control the status of the connected device with blue LED indication for enhanced visual control. LED technology ensures the maximum quality in terms of reliability, efficiency, maintenance and energy saving. No accessible electrical contact under the plate.

Advantages


- Plate and switch rocker in same metal: austenitic stainless steel Non magnetic Grade 304L
- Made in UK
- Delivered with screws for flush & surface boxes in both plastic and metal boxes

Documentation

TECHNICAL DOCUMENTATION

 F02657EN-00.pdf | PDF (0.15Mo)

Agreements & Certificates

 ASTA-880 | (0.24Mo)

CATALOGUE PAGE & OTHERS

 ex223001_0730.pdf | PDF (0.09Mo)