

Product sheet



LEGRAND

Remote control dimmer via BUS line - fluorescent lamp with 0-10V ballast - max 1000 VA - DIN 4 modules

REF. 003660 | EAN. 3245060036607

> [Visit e-catalogue](#)

Product characteristics

- For fluorescent lamps with 1 - 10V ballast (fluorescent tubes and compact fluorescent lamps with separated ballast)
- Ballast power : maximum 1000VA
- Mains voltage 100/240VAC - 50/60Hz
- DIN 4 modules
- Control current: 50 mA

The product's benefits

Installation

- Symmetrical rail mounting

Usage

- Equipped with illuminated scale indicating the light level of controlled lamps

Advantages

- Equipped with illuminated scale indicating the light level of controlled lamps

Documentation

TECHNICAL DOCUMENTATION

→ [0064JR4-03_FR.pdf](#) | PDF (0.52Mo)

→ [0064JR4-03_EN.pdf](#) | PDF (0.52Mo)

CAD & Design specs / BIM

 [003660.dwg](#) | DWG (0.1Mo)

CATALOGUE PAGE & OTHERS

 [ex223001_0108.pdf](#) | PDF (0.08Mo)