

Product sheet



SYNERGY™ LEGRAND

Synergy™ Sleek - universal rotary dimmer (LED & Halogen) - 300W - Brushed Stainless Steel

REF. 832151 | EAN. 3414970661449

> [Visit e-catalogue](#)

Product characteristics

- 100V~ to 250V~, 50/60Hz 5W to 75W for dimmable LED and fluocompact, 5W to 300W for halogen and incandescent
- Can be associated with one or several push - buttons, for ON/OFF or dimming control.
- Integrates memory level function : when switched ON, gradually (2 s) lights up at the level set before last switch OFF.
- Screwless cover plate is square 86x86 mm, product thickness is 4mm (once is installed onto the wall).
- Equipped with overvoltage and short-circuit protection

Recommendation / Restriction

- Recommended inside use only

The product's benefits

Installation

- Without neutral can be retro-fitted into existing point of lighting

Usage

- Rotary shaped knob for easy grip allowing the dimming of enabled charges (included LED charges)

Advantages

- Plate and knob in same metal: austenitic stainless steel Non magnetic Grade 304L
- Rotary dimmer for all type of lamps including dimmable LED and fluocompact
- Delivered with screws for flush & surface boxes in both plastic and metal boxes

Documentation

TECHNICAL DOCUMENTATION

→ LE08934AA_EN-AR.pdf | PDF (3.11Mo)

F02305EN-00.pdf | PDF (0.62Mo)

Agreements & Certificates

OC / CB-SE-115438 | (0.62Mo)

AoC-PRJ0072681 | (0.36Mo)

OC / CB-PRJ0072681 | (0.28Mo)

CATALOGUE PAGE & OTHERS

ex223001_0727.pdf | PDF (0.08Mo)