

Product sheet



SYNERGY™ LEGRAND

Synergy™ Authentic - Push on/off rotary dimmer - 1000W - Brushed Stainless Steel

REF. 833150 | EAN. 3414970665683

> [Visit e-catalogue](#)

Product characteristics

- 100V~ to 250V~ 50/60Hz 60W to 1000W (230V~)
- Screw type terminals for enhanced contacts
- Cover plate is square 86x86 mm, product thickness is 7mm (once is installed onto the wall).
- For flush-mounting, back box to be min. 35 mm deep.

Recommendation / Restriction

- Recommended inside use only

The product's benefits

Installation

- Strip length indicator avoids waste of wires. Terminal screws backed off ready to cabling

Avantages

- Plate and knob in same metal: austenitic stainless steel Non magnetic Grade 304L
- Made in UK
- Delivered with screws for flush & surface boxes in both plastic and metal boxes

Documentation

TECHNICAL DOCUMENTATION



F02304EN-00.pdf | PDF (0.64Mo)

CATALOGUE PAGE & OTHERS



ex223001_0722.pdf | PDF (0.09Mo)