

# Product sheet



LEGRAND

Receptacle for floor socket Arteur/Mosaic - round version - stainless steel

REF. 089701 | EAN. 3245060897017

> [Visit e-catalogue](#)

## Product characteristics

- Receptacles for floor sockets - Extra slim plate IP 44 - IK 08 - Equipped with a 180° opening flap - Extra flat finish : thickness 2 mm - Lighting base of receptacle by white LED - To be equipped with 2 modules square version Arteur or Mosaic functions : - socket outlets without cover, German, Euro - US, Swiss, Danish, Israeli and French standards - Double USB chargers - RJ 11 and RJ 12 sockets , Television sockets , RJ 45 sockets UTP, FTP and STP without controlled access - loudspeaker sockets - HDMI sockets or HD 15 sockets without jackRound receptacle - Stainless steel

## Documentation

### TECHNICAL DOCUMENTATION

-  F01511EN-07.pdf | PDF (0.97Mo)
-  F01511FR-07.pdf | PDF (0.97Mo)
-  LE04522AD.pdf | PDF (0.86Mo)

### Agreements & Certificates

-  LGRP-01153-V01.01-FR.pdf | PDF (0.65Mo)
-  NF-NF012\_3369 | (0.55Mo)

### CATALOGUE PAGE & OTHERS

-  ex223001\_1167.pdf | PDF (0.64Mo)