

Product sheet



LEGRAND

Cable ducting (base + cover) Transcab - 15x40 mm - grey RAL 7030

REF. 636096 | EAN. 3245066360966

> [Visit e-catalogue](#)

Product characteristics

- Transcab cable ducting - 6.5 mm wide fingers with a 6 mm spacing - Accepts up to 6 mm² without breaking side wall finger - Two pre - scored lines allow removal of fingers - Bump on side wall fingers help cabling - Rounded fingers prevent injury during cabling - Conform to EN 500 85 parts 2 and 3 - Plastic cable ducting (base + cover) - Side perforations at intervals of 12.5 mm - Length : 2 m
- Grey RAL 7030 - PVC - Width x Height : 15 x 40 mm - Capacity : 455 mm²

Documentation

TECHNICAL DOCUMENTATION



F01894EN-02.pdf | PDF (2.49Mo)



F01894FR-02.pdf | PDF (2.47Mo)

Agreements & Certificates



UL recogn-E212478 | (0.09Mo)



LGRP-01659-V01.01-EN.pdf | PDF (0.56Mo)



NF Conduits-641237C | (0.18Mo)

CATALOGUE PAGE & OTHERS



ex223001_0479.pdf | PDF (0.07Mo)