

# Product sheet



LEGRAND

Cable ducting (base + cover) Transcab - 120x80 mm - grey RAL 7030

REF. 636125 | EAN. 3245066361253

> [Visit e-catalogue](#)

## Product characteristics

- Transcab cable ducting - 6.5 mm wide fingers with a 6 mm spacing - Accepts up to 6 mm<sup>2</sup> without breaking side wall finger - Two pre-scored lines allow removal of fingers - Bump on side wall fingers help cabling - Rounded fingers prevent injury during cabling - Conform to EN 500 85 parts 2 and 3 - Plastic cable ducting (base + cover) - Side perforations at intervals of 12.5 mm - Length : 2 m
- Grey RAL 7030 - PVC - Width x Height : 120 x 80 mm - Capacity : 8729 mm<sup>2</sup>

## Documentation

### TECHNICAL DOCUMENTATION

 F01894EN-02.pdf | PDF (2.49Mo)

 F01894FR-02.pdf | PDF (2.47Mo)

### Agreements & Certificates

 UL recogn-E212478 | (0.09Mo)

 LGRP-01659-V01.01-EN.pdf | PDF (0.56Mo)

 NF 004-641237C | (0.18Mo)

### CATALOGUE PAGE & OTHERS

 ex223001\_0479.pdf | PDF (0.07Mo)