

Product sheet



ARTEOR™ LEGRAND

Arteor™ - British standard plate square version 2 modules - Soft Alu

REF. 571302 | EAN. 3414971241763



[> Visit e-catalogue](#)

Product characteristics














- Arteor British standard plates - 60,3 mm fixing centres
- For 2 module mechanism - To be associated with 1 gang flush-mounting box and support frame Cat. No 5 760 03 or 5 760 01 (for 2 module mechanisms to be mounted on 3 module support frame) - Neutral - Soft Alu

Documentation

TECHNICAL DOCUMENTATION

-  F03578EN-00.pdf | PDF (0.13Mo)
-  F03578FR-00.pdf | PDF (0.13Mo)

Agreements & Certificates

-  Decl. UE RED-A 4155 A | (0.45Mo)
-  OC / CB-FR_705030/A1 | (1.68Mo)
-  Decl. UE RED-A 4133 A | (0.64Mo)
-  OC / CB-FR_722636 | (0.35Mo)
-  OC / CB-JPTUV-165901-M2 | (0.58Mo)
-  LGRP-02145-V01.01-FR.pdf | PDF (0.79Mo)
-  OC / CB-FR_705038/M1 | (2.34Mo)
-  Decl. UE RED-A 4166 A | (0.45Mo)
-  Decl. UE RED-A 4144 A | (0.45Mo)
-  LGRP-01719-V01.01-EN.pdf | PDF (0.73Mo)
-  Decl. UE RED-A 3812 B | (0.25Mo)
-  LGRP-01108-V02.01-EN.pdf | PDF (0.83Mo)
-  OC / CB-FR_707098 | (0.67Mo)