

Product sheet



LEGRAND

Bulkhead light - IP44 - IK07 - round - E 27 - glass diffuser

REF. 060451 | EAN. 3245060604516

> [Visit e-catalogue](#)

Product characteristics

- IP 44/54/55 weatherproof bulkhead lights - For domestic, commercial areas and tough environments
- IP 44 - IK 07 round bulkhead lights - Polypropylene base - For 23 W compact fluorescent lamps - Diffuser is assembled by a 1/4 turn rotation - Porcelain lampholder - White - E 27 - Glass diffuser

Documentation

TECHNICAL DOCUMENTATION

→ [0064W4103.pdf](#) | PDF (0.39Mo)

→ [LE06955AA.pdf](#) | PDF (0.53Mo)

Agreements & Certificates

 [IRAM-DC-E-E100-008.1](#) | (1.06Mo)

 [LGRP-00119-V01.01-EN.pdf](#) | PDF (0.57Mo)

CATALOGUE PAGE & OTHERS

 [ex223001_0901.pdf](#) | PDF (0.09Mo)

 [ex223001_0902.pdf](#) | PDF (0.09Mo)