

Product sheet



LEGRAND

Bulkhead light - IP44 - IK06 - oval 100 W- E27 -metal grid screw fixing -grey

REF. 060419 | EAN. 3245060604196

> [Visit e-catalogue](#)

Product characteristics

- IP 44/54/55 weatherproof bulkhead lights - For domestic, commercial areas and tough environments
- Oval - IP 44 / IK 06 - Polypropylene base - Glass diffuser - Galvanised steel or plastic - Protection wire grid - 3 side knockable entries, for 16, 20 mm - cable - 230 V - 50 Hz - Self - extinguishing : 850 °C - For compact fluorescent lamps - Porcelain lampholder - Screw terminals 20 W - E 27 - Grey - Metal grid - screw Fixing

Documentation

TECHNICAL DOCUMENTATION

→ [LE03540AC.pdf](#) | PDF (0.57Mo)

Agreements & Certificates

 [LGRP-00123-V01.01-EN.pdf](#) | PDF (0.57Mo)

CATALOGUE PAGE & OTHERS

 [ex223001_0901.pdf](#) | PDF (0.09Mo)

 [ex223001_0902.pdf](#) | PDF (0.09Mo)