

Product sheet



LEGRAND

Bulkhead light Plexo - IP54 - IK08 - rectangular - 75 Wincandescent - red

REF. 062402 | EAN. 3245060624026

[> Visit e-catalogue](#)

Product characteristics

- IP 44/54/55 weatherproof bulkhead lights - For domestic, commercial areas and tough environments
- IP 54 - IK 08 Plexo rectangular bulkhead lights class II - Polycarbonate diffuser, mounted on hinge - Opening can be reversed Top/Base - Supplied with one Plexo end cap, not assembled - Through wiring or terminal connection (side or rear) - Lampholder mounted on reflector (swivel pull - out type) - Grey base self - extinguishing : 850 °C - For E27 - 55 W halogen, 17 W compact fluorescent or 8 W LED lamps - E 27 - With red diffuser

Documentation

TECHNICAL DOCUMENTATION

 S000092755FR_1.pdf | PDF (0.53Mo)

 LE12378AA.pdf | PDF (2.65Mo)

Agreements & Certificates

 LGRP-00122-V01.01-EN.pdf | PDF (0.56Mo)

 NF LUMINAIRES-NF105_1037 | (0.49Mo)

CATALOGUE PAGE & OTHERS

 ex223001_0901.pdf | PDF (0.09Mo)

 ex223001_0902.pdf | PDF (0.09Mo)