

Product sheet



LEGRAND

RCCB TX³ - 4P 400 V~ - 30 mA - 63 A - AC type - neutral on left-hand - no aux.

REF. 403006 | EAN. 3245064030069

> [Visit e-catalogue](#)

Product characteristics

- RCCBs TX³ - residual current circuit breakers - from 25 A to 63 A - AC and A types - Conform to IEC 61008 - 1 - Compatible with prong - type supply busbars - AC type : detect AC component faults - A type : detect AC and DC component faults - Do not accept auxiliaries
- 4-pole - 400 V~ - Neutral on left - hand sideAC type - Sensitivity : 30 mA - In : 63 A - Number of modules : 4

Documentation

TECHNICAL DOCUMENTATION

 F01542EN-01.pdf | PDF (0.6Mo)

CAD & Design specs / BIM

 403004.dwg | DWG (0.16Mo)

CATALOGUE PAGE & OTHERS

 ex223001_0055.pdf | PDF (0.08Mo)

Agreements & Certificates

 LGRP-02039-V01.01-EN.pdf | PDF (0.76Mo)

 OC / CB-CB FR_705078/M1 | (3.33Mo)

 VDE-40036431 | (0.39Mo)