

Product sheet



ATS LEGRAND

Automatic control switch control unit between two sources for DPX3 and DMX3 circuit breaker and CTX3 contactors

REF. 422683 | EAN. 3414970767820

> [Visit e-catalogue](#)

Product characteristics

- For advanced management of 3 breakers
- Interface LCD display, IR communication port on the Front panel for connection of USB or WiFi modules
- Power supply : 12 - 48 Vdc ; 100 - 240 Vac
- IP20
- Can be configured with the help of front panel touch keys or of the Legrand dedicated software

The product's benefits

Installation

- DPX3 platform has been developed to give a new solution of protection devices for a more precise approach in power installations in order to offer the correct answer for different project needs.

Usage

- DPX3 platform provide a complete "project" approach in premium market segment, offering a range completely suitable for high power application

Avantages

- DPX3 630 is the answer for the competition in the project sub-segment. A unique size for all versions (thermal magnetic, electronic with or without measure). Earth leakage fetures can be achieved by adding a dedicated module at the bottom of the breaker itself.

Documentation

TECHNICAL DOCUMENTATION

-  LE09863AA.pdf | PDF (4.55Mo)
-  LE09478AA_FR.pdf | PDF (4.9Mo)
-  LE09478AA_EN.pdf | PDF (2.5Mo)
-  EXB17039_GT_TransferSwitching.pdf | PDF (17.73Mo)
-  F02233FR_01_ATS_EVO_FRA.pdf | PDF (1.24Mo)

CATALOGUE PAGE & OTHERS

-  ex223001_0223.pdf | PDF (0.05Mo)
-  ex223001_0222.pdf | PDF (0.1Mo)

→ [LE09508AA_EN.pdf](#) | PDF (1.38Mo)

→ [LE09130AB.pdf](#) | PDF (1.79Mo)

 [LE09380AA.pdf](#) | PDF (5.36Mo)

 [LE09877AA.pdf](#) | PDF (3.79Mo)

Software & configurators

 [Acu Configurator.zip](#) | ZIP (99.82Mo)