

# Product sheet



LINKEO LEGRAND

Vertical wallmounting cabinet 19 inches 3U + 1U

REF. 646240 | EAN. 3414971599123

> [Visit e-catalogue](#)

## Product characteristics

- Equipped with front 3U 19" uprights for patch panels and active equipments. Additionnal rear 1U 19" uprights to install a PDU.
- Metallic door with integrated key lock.
- Perforations for natural ventilation. Can also house fan kit 0 462 60 and thermostat 0 348 48.
- 3 pre-cut cable entries (sides and rear).
- Anthracite grey RAL 7016

## Recommendation / Restriction

- For indoor use only.

## The product's benefits

### Installation

- The door can be totally removed and thus, to access inside the cabinet for cabling is very convenient.

### Usage

- Fixed vertically on wall, its very small depth (158mm) and timeless design make this cabinet very easy to integrate in any space.

### Advantages

- Continuity of the cabinet metal conductive parts is achieved by design. The equipotential link of the back base is created with the spiked washer supplied.
- Excellent resistance of the paint coating to impacts, scratches and cleaning agents.

## Documentation

### TECHNICAL DOCUMENTATION

- [LE11475AB.pdf](#) | PDF (4.57Mo)
-  [S000106510EN-00.pdf](#) | PDF (0.16Mo)
-  [S000106510FR-00.pdf](#) | PDF (0.16Mo)

### CATALOGUE PAGE & OTHERS

-  [ex223001\\_0946.pdf](#) | PDF (0.09Mo)