

Product sheet



BELANKO S LEGRAND

Belanko S - universal rotary dimmer (LED & Halogen) - 300W - White

REF. 617635 | EAN. 3414971684584

> [Visit e-catalogue](#)

Product characteristics

- 150 W, 127 V / 37W LED)
- Sold with white BELANKO S plate
- Screw type terminals for enhanced contacts
- Marked terminals for easy identification
- Rotary shaped knob for easy grip without neutral

Recommendation / Restriction

- Recommended inside use only

The product's benefits

Installation

- Can be retro-fitted into existing point of lighting

Usage

- Allows the dimming of enabled charges (incl. LED charges) from 10 to 100%

Advantages

- Fast and Easy install. Paint job made simpler
- Optimised range for new builds and ideal for renovation projects
- Delivered with screws for flush & surface boxes in both plastic and metal boxes

Documentation

TECHNICAL DOCUMENTATION

 F02988EN-01.pdf | PDF (0.83Mo)

Agreements & Certificates

 OC / CB-SE-115438 | (0.62Mo)

 AoC-PRJ0072681 | (0.36Mo)

 OC / CB-SE-96305 | (0.99Mo)

 OC / CB-PRJ0072681 | (0.28Mo)

CATALOGUE PAGE & OTHERS

 ex223001_0671.pdf | PDF (0.05Mo)