

# Product sheet



## BELANKO S LEGRAND

Belanko S - universal rotary dimmer (LED & Halogen) - 300W - White

REF. 617635 | EAN. 3414971684584

> [Visit e-catalogue](#)

## Product characteristics

- 150 W, 127 V / 37W LED)
- Sold with white BELANKO S plate
- Screw type terminals for enhanced contacts
- Marked terminals for easy identification
- Rotary shaped knob for easy grip without neutral

## Recommendation / Restriction

- Recommended inside use only

## The product's benefits

### Installation

- Can be retro-fitted into existing point of lighting

### Usage

- Allows the dimming of enabled charges (incl. LED charges) from 10 to 100%

### Advantages

- Fast and Easy install. Paint job made simpler
- Optimised range for new builds and ideal for renovation projects
- Delivered with screws for flush & surface boxes in both plastic and metal boxes

## Documentation

### TECHNICAL DOCUMENTATION

 F02988EN-01.pdf | PDF (0.83Mo)

### Agreements & Certificates

 OC / CB-SE-115438 | (0.62Mo)

 OC / CB-SE-96305 | (0.99Mo)

### CATALOGUE PAGE & OTHERS

 ex223001\_0671.pdf | PDF (0.05Mo)