

Product sheet



BELANKO S LEGRAND

Belanko S rotary dimmer incan/ halogen - 1000W - Ivory

REF. 617831 | EAN. 3414971689398

> [Visit e-catalogue](#)

Product characteristics

- 500W to 1000 W, 127/230 V
- Sold with white BELANKO S plate
- Screw type terminals for enhanced contacts
- Marked terminals for easy identification
- Rotary shaped knob for easy grip without neutral

Recommendation / Restriction

- Recommended inside use only

The product's benefits

Installation

- Can be retro-fitted into existing point of lighting

Usage

- Allows the dimming of enabled charges from 10 to 100%

Advantages


- Fast and Easy install. Paint job made simpler
- Optimised range for new builds and ideal for renovation projects
- Delivered with screws for flush & surface boxes in both plastic and metal boxes


Documentation

TECHNICAL DOCUMENTATION

 F02988EN-01.pdf | PDF (0.83Mo)

Agreements & Certificates

 OC / CB-SE-96079A1 | (0.07Mo)

 OC / CB-FR_711878/M1 | (0.19Mo)

 OC / CB-FR-711878 | (0.53Mo)

 OC / CB-SE-96079 | (0.47Mo)

 OC / CB-SE-105293 | (0.5Mo)

CATALOGUE PAGE & OTHERS

 ex223001_0671.pdf | PDF (0.05Mo)