

Product sheet



BELANKO S LEGRAND

Belanko S 4 gang 2-way switch - 16AX - Ivory

REF. 617807 | EAN. 3414971688735

> [Visit e-catalogue](#)

Product characteristics

- 16AX, 250V
- Sold with white BELANKO S plate
- Screw type terminals for enhanced contacts
- Marked terminals for easy identification

Recommendation / Restriction

- Recommended inside use only

The product's benefits

Installation

- Practical 4-point lighting control on a single plate.
- Quick & Easy plate clipping system

Usage

- No accessible electrical contact under the rockers.
- Practical 4-point lighting control on a single plate.

Advantages

- Innovative all-in-one face plate & rocker. Fast and Easy install. Paint job made simpler
- Optimised range for new builds and ideal for renovation projects
- Delivered with screws for flush & surface boxes in both plastic and metal boxes

Documentation

TECHNICAL DOCUMENTATION

→ [LE13288AA.pdf](#) | PDF (1.45Mo)

 [F02968EN-02.pdf](#) | PDF (0.59Mo)

Agreements & Certificates

 [LGRP-00923-V01.01-EN.pdf](#) | PDF (0.6Mo)

 [SNI-PCS 00081.02](#) | (1.43Mo)

 [OC / CB-CN52153-A1/M1](#) | (0.32Mo)

 [OC / CB-CN46302](#) | (0.38Mo)

CATALOGUE PAGE & OTHERS

 [ex223001_0669.pdf](#) | PDF (0.08Mo)



OC / CB-CN52153 | (0.3Mo)