

Product sheet



BELANKO S LEGRAND

Belanko S - 2 gang single pole BS switched socket outlet inboard - 13A + USB type A+C - White

REF. 617644 | EAN. 3414971684829

> [Visit e-catalogue](#)

Product characteristics

- 2P+E British Standard, 13A, 250V + 2,4A A+C USB charger
- Sold with white BELANKO S plate
- Screw type terminals for enhanced contacts
- Marked terminals for easy identification
- Switch allows safe disconnection of an electrical appliance and the convenient charging of A + C type USB devices (USB Output =2.4A)

Recommendation / Restriction

- Recommended inside use only

The product's benefits

Installation

- Quick & Easy installation in a double wall box installation

Usage

- Fitted with safety shutters to maximise child protection + Convenient charging of both A&C USB devices

Advantages

- Delivered with its protective shell against paint and dust during installation phase
- Optimised range for new builds and ideal for renovation projects
- Delivered with screws for flush & surface boxes in both plastic and metal boxes

Documentation

TECHNICAL DOCUMENTATION

 F02982EN-01.pdf | PDF (0.92Mo)

Agreements & Certificates

 OC / CB-SE-104641M1 | (0.09Mo)

 OC / CB-SE-104641 | (1.37Mo)

 OC CEM / CB EMC-220300363SHA-V1 | (0.6Mo)

 G-MARK-0048-1399-V-1 | (15.67Mo)

CATALOGUE PAGE & OTHERS

 ex223001_0674.pdf | PDF (0.08Mo)



OC / CB-SE-102292 | (0.09Mo)