

Product sheet



BELANKO S | LEGRAND

Belanko S - 2 gang single pole BS switched socket outlet inboard rockers - 13A - Anthracite

REF. 617746 | EAN. 3414971687349

> [Visit e-catalogue](#)

Product characteristics

- 2p+E British Standard, 13A, 250V
- Sold with white BELANKO S plate
- Screw type terminals for a secured & enhanced contacts
- Marked terminals for easy identification
- Switch allows safe disconnection of an electrical appliance

Recommendation / Restriction

- Recommended inside use only

The product's benefits

Installation

- Quick & Easy plate clipping system

Usage

- Fitted with safety shutters to maximise child protection

Advantages

- Delivered with its protective shell against paint and dust during installation phase
- Optimised range for new builds and ideal for renovation projects
- Delivered with screws for flush & surface boxes in both plastic and metal boxes

Documentation

TECHNICAL DOCUMENTATION

 F02973EN-01.pdf | PDF (0.52Mo)

Agreements & Certificates

 OC / CB-SE-90908M1 | (1.02Mo)

 OC / CB-FR_719315 | (0.61Mo)

 OC / CB-CN48885-M1 | (0.61Mo)

 LGRP-00925-V02.01-EN.pdf | PDF (0.72Mo)

 AoC-2466AS05ARLI54958-N2 | (0.33Mo)

CATALOGUE PAGE & OTHERS

 ex223001_0674.pdf | PDF (0.08Mo)