

Product sheet



MOSAIC™ WITH NETATMO LEGRAND

Mosaic™ with Netatmo - Wireless motion sensor

REF. 574252 | EAN. 3414971756991

> [Visit e-catalogue](#)

Product characteristics

- Quick and easy pairing with wired products (connected switch with dimmer option, connected power outlet, connected micromodule, or connected cable outlet)
- Sensor for controlling power outlets and lights (indoors and outdoors - IP44)
- Supplied with 2 x 1.5 V AA batteries. Battery life 2 years
- 140° infrared detection adjustable from 2 to 8 m. Light level threshold adjustable from 1 to 1000 lux
- LED indicator with low battery warning. White

Recommendation / Restriction

- To connect your wireless motion sensor, you first need to purchase and install a Mosaic with Netatmo connected starter pack. The wireless motion sensor allows you to switch on lights and electrical appliances. Does not control roller shutters. Can be paired with connected switches with dimmer option, connected power outlets, connected micromodules, or connected cable outlets (up to 20 appliances per sensor)

The product's benefits

Installation

- Easily position your wireless motion sensor on an indoor or outdoor wall

Usage

- Create a customised illuminated path both inside and outside your house.

Documentation

TECHNICAL DOCUMENTATION

→ LE11948AA.pdf | PDF (2.81Mo)

📄 F02925EN-00.pdf | PDF (0.14Mo)

Agreements & Certificates

📄 Decl. UE RED-A 3983 A | (0.09Mo)

📄 OC / CB-DE 2-044157 | (0.43Mo)

CATALOGUE PAGE & OTHERS

📖 ex223001_0627.pdf | PDF (0.12Mo)

📖 ex223001_0610.pdf | PDF (0.15Mo)