

# Product sheet



PLEXO™ LEGRAND

Plexo™ - 2-gang surface box with 4 membrane glands (3 x 1 entry + 1 x 2 entries) - Horizontal and vertical - IP55 - Grey

REF. 069672L | EAN. 3414971881198

The grey waterproof 2-gang box Plexo allows a surface mounting of all Plexo functions (mechanism products). This box conception gives the opportunity to install it horizontally or vertically. For indoor or outdoor use.

> [Visit e-catalogue](#)

## Description

The grey waterproof 2-gang box Plexo allows a surface mounting of all Plexo functions (mechanism products). This box conception gives the opportunity to install it horizontally or vertically. For indoor or outdoor use.

### Product characteristics

- Surface box to install functions supplied in composable mode (mechanism products).
- IP55 : protected against dust and water spary from all directions.
- Plastic materials with reinforced UV protection

## The product's benefits

### Installation

- A two-part box : a thin and very rigid mounting plate allows an easy fixing and a freedom of movement for wiring (the flexible part on the back of the product adapts to the shape of the wall) and a frame, to be clipped on the mounting plate.

### Usage

- The box can be used for both vertical and horizontal installation thanks to the 90° symmetrical mechanisms.

### Avantages

- The box is composed of a mounting plate and a frame. The thin and very rigid mounting plate allows an easy fixing and a freedom of movement for wiring. The flexible part on the back of the product adapts to the shape of the wall.
- The box can be used for both vertical and horizontal installation thanks to the 90° symmetrical mechanisms.

## Documentation

### TECHNICAL DOCUMENTATION

 F03421EN-02.pdf | PDF (1.91Mo)

 F03421FR-02.pdf | PDF (1.9Mo)

CAD & Design specs / BIM

### CATALOGUE PAGE & OTHERS

 ex223001\_0795.pdf | PDF (0.15Mo)

Agreements & Certificates

-  3D\_LG-069672L.stp | IFC (1.14Mo)
- BIM-LEGRAND-PLEXO-2025-FRANCAIS.rvt | RVT (135.87Mo)
- BIM-LEGRAND-PLEXO-2025-ENGLISH.rvt | RVT (137.72Mo)

-  MEEI-UP 69267307 002 | (1.25Mo)
-  AENOR-030/002621 | (0.71Mo)
-  OC / CB-FR\_715939 | (0.64Mo)
-  MEEI-UP 69267307 001 | (1.57Mo)
-  OC / CB-FR\_715726 | (0.74Mo)
-  LGRP-01292-V02.01-FR.pdf | PDF (0.82Mo)
-  NF App Domestic-NF012\_3249/A1 | (0.7Mo)
-  VDE-40057978 | (1.18Mo)
-  NF App Domestic-NF012\_3294/A2 | (0.74Mo)
-  OC / CB-FR\_718712/A1 | (0.55Mo)
-  Decl. UE RED-A 4229 A | (0.45Mo)
-  MEEI-UP 69267307 003 | (1.57Mo)