

Product sheet



PLEXO™ LEGRAND

Plexo™ - 2-gang surface box with 1 double M20 and 1 flexible membrane gland - Horizontal and vertical - IP55 - Grey

REF. 069668L | EAN. 3414971881105

The grey waterproof 2-gang box M20 Plexo allows a surface mounting of all Plexo functions. This box conception gives the opportunity to wire the mechanisms from the top, bottom, sides or back of the box. For indoor or outdoor use.

> [Visit e-catalogue](#)

Description

The grey waterproof 2-gang box M20 Plexo allows a surface mounting of all Plexo functions. This box conception gives the opportunity to wire the mechanisms from the top, bottom, sides or back of the box. For indoor or outdoor use.

Product characteristics

- Surface box to install functions supplied in composable mode (mechanism products).
- IP55 : protected against dust and water spary from all directions.
- Plastic materials with reinforced UV protection

The product's benefits

Installation

- A two-part box : a thin and very rigid mounting plate allows an easy fixing and a freedom of movement for wiring (the flexible part on the back of the product adapts to the shape of the wall) and a frame, to be clipped on the mounting plate.

Usage

- The box can be used for both vertical and horizontal installation thanks to the 90° symmetrical mechanisms.

Avantages

- The box is composed of a mounting plate and a frame. The thin and very rigid mounting plate allows an easy fixing and a freedom of movement for wiring. The flexible part on the back of the product adapts to the shape of the wall.
- The box can be used for both vertical and horizontal installation thanks to the 90° symmetrical mechanisms.

Documentation

TECHNICAL DOCUMENTATION

 F03421EN-02.pdf | PDF (1.91Mo)

 F03421FR-02.pdf | PDF (1.9Mo)

CAD & Design specs / BIM

CATALOGUE PAGE & OTHERS


 ex223001_0795.pdf | PDF (0.15Mo)

Agreements & Certificates


BIM-LEGRAND-PLEXO-2025-FRANCAIS.rvt | RVT (135.87Mo)

 3D_LG-069668L.stp | IFC (1.22Mo)

BIM-LEGRAND-PLEXO-2025-ENGLISH.rvt | RVT (137.72Mo)

 NF App Domestic-NF012_3249/A1 | (0.7Mo)

 AENOR-030/002621 | (0.71Mo)

 VDE-40057978 | (1.18Mo)

 NF App Domestic-NF012_3294/A2 | (0.74Mo)

 OC / CB-FR_715939 | (0.64Mo)

 OC / CB-FR_718712/A1 | (0.55Mo)

 OC / CB-FR_715726 | (0.74Mo)