

Product sheet



ARTEOR™ LEGRAND

Arteor™ - Electronic room thermostat - 2 modules - Champagne

REF. 572706 | EAN. 3414971847675

> [Visit e-catalogue](#)

Product characteristics

- Arteor ventilation, heating, roller blinds control, RCBO and MCB - Mechanisms supplied with rocker plates, to be equipped with support frames and plates
- Thermostats Electronic room thermostat - Control knob with index and adjustable segments for min. and max. settings - Adjustable range from 5 °C to 30 °C (+/- 0,5 °C) - Power supply : 230 V~ - 50/60 Hz - One potential free changeover contact output - Suitable for controlling heated ceilings and underfloor heating - LV use breaking capacity : - 8 A - 250 V~ - resistive inductive circuit - 2 A - 250 V~ - inductive circuit - ELV use breaking capacity : - 12 to 48 VA - 12 to 24 V, from 1 mA min. to 500 mA max. - 2 modules - Champagne

Documentation

TECHNICAL DOCUMENTATION

 F01858EN-01.pdf | PDF (1.69Mo)

 292373-05.pdf | PDF (1.46Mo)

CATALOGUE PAGE & OTHERS

 ex223001_0566.pdf | PDF (0.09Mo)