

Product sheet



PLEXO™ LEGRAND

Plexo™ - double prewired horizontal german standard socket-outlet 16A 250V - Mechanism - Grey

REF. 069576L | EAN. 3414971879249

The grey Plexo composable waterproof double socket-outlet can be used to connect electrical or electronic equipment in any location where resistance to water, dust and impact is required. For indoor or outdoor use.

> [Visit e-catalogue](#)

Description

The grey Plexo composable waterproof double socket-outlet can be used to connect electrical or electronic equipment in any location where resistance to water, dust and impact is required. For indoor or outdoor use.

Product characteristics

- Product to be completed either with a surface-mounted box or a flush-mounted support frame.
- IP55: protected against dust and water spray from all directions
- IK08: 5 joules shock resistance.
- 2P+E 16A 250V socket outlet. Automatic terminals : quick connection without tools with colour coding.

The product's benefits

Installation

- The mechanism is easy to install without tools and can be removed by simply pressing on the sides. The clipping system ensures high resistance to wire pressure.

Usage

- Two pre-wired sockets: only 1 mechanism to be wired.

Avantages

- A prewired socket with no visible connecting wire for simpler wiring.
- A 4-point (1/4 turn) front closure to ensure waterproofness whatever the configuration of the installation.

Documentation

TECHNICAL DOCUMENTATION

F03973FR-00.pdf | PDF (1.31Mo)

F03973EN-00.pdf | PDF (1.31Mo)

CAD & Design specs / BIM

BIM-LEGRAND-PLEXO-2025-FRANCAIS.rvt | RVT (135.87Mo)

3D_LG-069576L.stp | IFC (1.36Mo)

BIM-LEGRAND-PLEXO-2025-ENGLISH.rvt | RVT (137.72Mo)

CATALOGUE PAGE & OTHERS

ex223001_0794.pdf | PDF (0.11Mo)

Agreements & Certificates

OC / CB-FR_718712/A1 | (0.55Mo)

KSC-JW04001-24002 | (4.69Mo)

AENOR-030/002645 | (0.59Mo)



VDE-40059394 | (0.44Mo)