

# Product sheet



ARTEOR™ WITH NETATMO LEGRAND

Arteor™ with Netatmo - Connected switch with neutral (with dimmer option) 150W, 1 module - Champagne

REF. 574343 | EAN. 3414971961852

> [Visit e-catalogue](#)

## Product characteristics

- Max load power : 150W under 230V~, all loads leds included
- Compatible with traditional or dimmable bulbs, including LED. Dimmer activatable via Home + Control App
- LED indicator with locator function which can be activated in the app
- Equipped with an auxiliary entry for a mechanical push button
- Radio technology 2.4GHz, using Zigbee 3.0 protocol, reliable and secure

## Recommendation / Restriction

- To connect your connected switch with neutral (with dimmer option), it is necessary to purchase and install a ARTEOR with Netatmo connected starter pack beforehand. To control it as a 2 way switch, it is necessary to associate one or more ARTEOR with Netatmo wireless commands to it and / or wire it with a mechanical push button.

## The product's benefits

### Installation

- The ARTEOR with Netatmo connected switch with neutral (with dimmer option) is easily installed in place of an existing switch and requires a standard depth flush mounting box (40mm). Compatible with claw frames. Does not require the installation of a bleeder

### Usage

- Control your lights with your voice using a vocal assistant

### Avantages

- Perfect aesthetic integration with the installed wiring devices
- Using ON/OFF mode, compatible with all type of loads, dimmable or not
- Very easy to use with multi-zone ergonomics

## Documentation


### TECHNICAL DOCUMENTATION

 F03166EN-02.pdf | PDF (0.13Mo)

 LE12093AC.pdf | PDF (1.4Mo)

### Agreements & Certificates

 Decl. UE RED-A 3955 A | (0.2Mo)

 OC / CB-DE 2-031067 | (0.66Mo)

### CATALOGUE PAGE & OTHERS

 ex223001\_0607.pdf | PDF (0.1Mo)

