

Product sheet



LEGRAND

**DRX 630 adjustable thermal magnetic MCCB -
breaking capacity Icu 36 kA - 415 V~ - 3P - In 400 A**

REF. 667651 | EAN. 3414970673534

> [Visit e-catalogue](#)

Product characteristics

- DRX 630 adjustable - thermal magnetic MCCBs from 320 to 630 A - For switching, control, isolation and protection of low - voltage electrical lines - Can be fitted with auxiliaries - Supplied with : - Screw terminals - Fixing screws - Insulating shields (2 for 3P and 3 for 4P) - Adjustable thermal and magnetic - Conform to IEC 60947 - 2
- DRX 630 - Thermal adjustable from 0,8 to 1 x In - Magnetic adjustable from 5 to 10 x In. Breaking capacity Icu 36 kA (415 V~) - 3P - 400 A

Documentation

TECHNICAL DOCUMENTATION

- [LE07105AA.pdf](#) | PDF (2.2Mo)
-  [F02406EN00_DRX630_adjENG_v2.0.pdf](#) | PDF (0.57Mo)

CAD & Design specs / BIM

-  [027245.dwg](#) | DWG (0.23Mo)

CATALOGUE PAGE & OTHERS

-  [ex223001_0144.pdf](#) | PDF (0.03Mo)
-  [ex223001_0142.pdf](#) | PDF (0.06Mo)
-  [ex223001_0134.pdf](#) | PDF (0.08Mo)

Agreements & Certificates

-  [OC / CB-SE-91829](#) | (1.1Mo)