

Product sheet



LEGRAND

Thermal magnetic MCCB DRX 250 HP adjustable -
breaking capacity 50kA - 3P - 200A

REF. 669091 | EAN. 3414970860378

> [Visit e-catalogue](#)

Product characteristics

- DRX 250 HP adjustable - thermal magnetic MCCBs from 16 to 250 A - For switching, control, isolation and protection of low - voltage electrical lines - Can be fitted with auxiliaries - Supplied with : screw terminals, fixing screws, insulating shields (2 for 3P and 3 for 4P) - Adjustable thermal and magnetic - Conform to IEC 60947 - 2
- DRX 250 HP - Thermal adjustable from 0,8 to 1 x In - Magnetic adjustable from 5 to 10 x In. Breaking capacity Icu 50 kA (415 V~) - 3P - In : 200 A

Documentation

CATALOGUE PAGE & OTHERS

-  [ex223001_0157.pdf](#) | PDF (0.04Mo)
-  [ex223001_0154.pdf](#) | PDF (0.05Mo)
-  [ex223001_0148.pdf](#) | PDF (0.11Mo)
-  [ex223001_0156.pdf](#) | PDF (0.03Mo)

Agreements & Certificates

-  [LGRP-01194-V01.01-EN.pdf](#) | PDF (0.66Mo)

CAD & Design specs / BIM

-  [669410.dwg](#) | DWG (0.24Mo)
-  [669080.dwg](#) | DWG (0.19Mo)