

Product sheet



LEGRAND

Thermal magnetic MCCB DRX 125 HP adjustable -
breaking capacity 36kA - 3P - 25A

REF. 669722 | EAN. 3414971164307

> [Visit e-catalogue](#)

Product characteristics

- DRX 125 HP adjustable - thermal magnetic MCCBs from 16 to 125 A - For switching, control, isolation and protection of low - voltage electrical lines - Can be fitted with auxiliaries - Supplied with : screw terminals, fixing screws, insulating shields (2 for 3P and 3 for 4P) - Adjustable thermal - Fixed magnetic - Conform to IEC 60947 - 2
- DRX 125 HP - Thermal adjustable from 0,8 to 1 x In. Breaking capacity Icu 36 kA (415 V~) - 3P - In : 25 A

Documentation

CATALOGUE PAGE & OTHERS

-  [ex223001_0150.pdf](#) | PDF (0.05Mo)
-  [ex223001_0146.pdf](#) | PDF (0.11Mo)
-  [ex223001_0152.pdf](#) | PDF (0.03Mo)
-  [ex223001_0153.pdf](#) | PDF (0.04Mo)

CAD & Design specs / BIM

-  [669360.dwg](#) | DWG (0.19Mo)
-  [669720.dwg](#) | DWG (0.19Mo)