

Product sheet



GALION LEGRAND

Galion - 2 gangs cooker unit control - 45A Double Pole switch with British Standard 13A switched socket outlet - Matt Black

REF. 282425-C | EAN. 3414971854499

> [Visit e-catalogue](#)

Product characteristics

- British Standard 13A, 250V~ and 45A Switch
- Sold complete under one catalog number, ready to install.
- Screw terminals accept wires up to 10mm² for secure and enhanced contacts
- Marked terminals for easy identification
- Strip length indicator avoids waste of wires

Recommendation / Restriction

- Recommended inside use only

The product's benefits

Installation

- Honeycomb design supporting frame for stability and rigidity

Usage

- Complies to British Standards certification for heavy loads. Fitted with safety shutters to maximise child protection

Advantages

- Equivalent aesthetic as all other functions
- Product delivered with paint and dust protection
- Delivered with screws for flush-mounting or surface-mounting boxes, plastic or metal

Documentation

TECHNICAL DOCUMENTATION

 F03016EN-00 45A Cooker Unit.pdf | PDF (0.87Mo)

Agreements & Certificates

 OC / CB-FR_707922/M1 | (0.54Mo)

 AoC-2501B1368SHA-V1 | (0.59Mo)

 OC / CB-FR_707922 | (0.58Mo)

 G-MARK-0032-1873-V-1 | (11.21Mo)

 OC / CB-FR_719319 | (0.72Mo)

 OC / CB-FR_719316 | (0.77Mo)

CATALOGUE PAGE & OTHERS

 ex223001_0679.pdf | PDF (0.08Mo)

