

# Product sheet



## GALION LEGRAND

Galion - 1 gang 5 to 300 watts -incandescent or 5 to 75 watts led rotary dimmer -100-240 volts - 50/60 HZ - Rose Gold

REF. 282419-C1 | EAN. 3414971854314

> [Visit e-catalogue](#)

## Product characteristics

- 100V~ to 250V~, 50/60Hz 5W to 75W for dimmable LED and fluocompact, 5W to 300W for halogen and incandescent
- Sold complete under one catalog number, ready to install.
- Screw type terminals for enhanced contacts, marked terminals for easy identification
- Honeycomb design supporting frame for stability and rigidity
- Equipped with overvoltage and short-circuit protection

## Recommendation / Restriction

- Recommended inside use only

## The product's benefits

### Installation

- Without neutral can be retro-fitted into existing point of lighting

### Usage

- Integrates memory level function: when switched ON, gradually (2 s) lights up at the level set before last switch OFF.

### Advantages

- Rotary shaped knob for easy grip allowing the dimming of all type of lamps including dimmable LED and fluocompact
- Can be associated with one or several push-buttons, for ON/OFF or dimming control.
- Delivered with screws for flush-mounting or surface-mounting boxes, plastic or metal

## Documentation

### TECHNICAL DOCUMENTATION

 F02866EN-01 Dimmer & Fan control.pdf | PDF (0.87Mo)

### Agreements & Certificates

 OC / CB-SE-115438 | (0.62Mo)

 AoC-PRJ0072681 | (0.36Mo)

 OC / CB-SE-96305 | (0.99Mo)

 OC / CB-PRJ0072681 | (0.28Mo)

### CATALOGUE PAGE & OTHERS

 ex223001\_0679.pdf | PDF (0.08Mo)

