

# Product sheet



XL<sup>3</sup> LEGRAND

Modular distribution block with staggered bars 100 A - 7 connections per busbar - 4 modules

REF. 400405 | EAN. 3414971978546

> [Visit e-catalogue](#)

## Product characteristics

- Input 10 - 25 mm<sup>2</sup> solid or 6 - 16 mm<sup>2</sup> stranded, with or without ferrule
- 6 Output : 1 x 10 - 25 + 5 x 2.5 - 10 mm<sup>2</sup> rigid conductor
- 6 output : 1 x 6 - 16 + 5 x 1.5 - 10 mm<sup>2</sup> flexible conductor with or without ferrule
- In = 100A - 40°C Ui = 500 V
- Ipk = 26 kA - 60 ms Icw = 4,5 kA - 1s

## The product's benefits

### Installation

- Easy and fast cabling and connecting thanks to a maximised cabling space , optimized "orientation" of bars and adapted dimensions and positions of connections

### Usage

- Transparent , removable and 180° rotating cover to adapt to all wiring situations

### Avantages

- Maximised internal space and optimised bar orientation for easy cable access
- Connections sized and positioned to facilitate connection and answer all needs
- integrated system, to avoid accidental unscrewing of non connected screws

## Documentation

### TECHNICAL DOCUMENTATION

 F03358EN-02.pdf | PDF (2.35Mo)

 F03358FR-02.pdf | PDF (1.79Mo)

### CAD & Design specs / BIM

 400405.dwg | DWG (0.32Mo)

### CATALOGUE PAGE & OTHERS

 ex223001\_0299.pdf | PDF (0.13Mo)