

Product sheet



DSX SD 320 LEGRAND

DSX Switch disconnecter SD Frame 2(320A) - 4 poles
- Rated current = 200A - fixing on plate

REF. 424023 | EAN. 3414971920880

> [Visit e-catalogue](#)

Product characteristics

- Rated insulation voltage $U_i = 1000V$, rated impulse withstand voltage $U_{imp} = 12kV$, dielectric strength 50 Hz 1 min = 10kV
- Climatic condition according to IEC/EN 60947 - 1 Annex Q, Cat. F subject to temperature, humidity, vibration, shock and salt mist.
- Answer for standard market needs, compact design, innovation, total coordination with legrand mccb and mcb ranges
- Complete range of accessories: auxiliary contacts(NO+NC), rotary handles, locking accessory, sealable terminal shields IP40, phase barriers, spreaders

The product's benefits

Usage

- Distribution, MCC(Motor Control Center), HVAC (Heating, Ventilation and Air Conditionning)

Advantages

- Full integrated with XL³S
- Complies with the new standard IEC 60947-3:2020
- Common features with DPX³

Documentation

TECHNICAL DOCUMENTATION

 F03668EN_03.pdf | PDF (2.02Mo)

 LE14017AA.pdf | PDF (3.31Mo)

CAD & Design specs / BIM

 424023.dwg | DWG (0.17Mo)

CATALOGUE PAGE & OTHERS

 ex223001_0241.pdf | PDF (0.12Mo)

 ex223001_0238.pdf | PDF (0.14Mo)