

# Product sheet



DSX TSE 63 LEGRAND

DSX Transfer switching equipment TSE Frame 1 ( 63A)  
- 4 poles - Rated current = 40A - mounting on DIN rail

REF. 424107 | EAN. 3414971939110

> [Visit e-catalogue](#)

## Product characteristics

- Rated insulation voltage  $U_i = 1000V$ , rated impulse withstand voltage  $U_{imp} = 8kV$ , dielectric strength 50 Hz 1 min = 8kV
- Climatic condition according to IEC/EN 60947 - 1 Annex Q, Cat. F subject to temperature, humidity, vibration, shock and salt mist.
- Answer for standard market needs, compact design, innovation with pop up indicators ,total coordination with legrand mccb and mcb ranges
- Complete range of accessories: auxiliary contacts(NO+NC), rotary handles, sealable terminal shields IP30

## The product's benefits

### Usage

- Application on manage of loads (normal/emergency), motor earthing and phase inversion, ensure continuity of electrical system.

### Avantages

- Full integrated with XL<sup>3</sup> & XL<sup>3</sup>S

## Documentation

### TECHNICAL DOCUMENTATION


 F04092EN-00\_DSX\_TSE\_DIN.pdf | PDF (1.68Mo)


→ LE13538AA.pdf | PDF (2.86Mo)

### Agreements & Certificates

 OC / CB-SE-111974 | (0.28Mo)

### CATALOGUE PAGE & OTHERS

 ex223001\_0236.pdf | PDF (0.1Mo)

 ex223001\_0240.pdf | PDF (0.09Mo)