

Product sheet



DSX TSE 160 LEGRAND

DSX Transfer switching equipment TSE Frame 2(160A)
- 4 poles - Rated current = 100A - mounting on DIN rail

REF. 424109 | EAN. 3414971939158

> [Visit e-catalogue](#)

Product characteristics

- Rated insulation voltage $U_i = 1000V$, rated impulse withstand voltage $U_{imp} = 8kV$, dielectric strength 50 Hz 1 min = 8kV
- Climatic condition according to IEC/EN 60947 - 1 Annex Q, Cat. F subject to temperature, humidity, vibration, shock and salt mist.
- Answer for standard market needs, compact design, innovation with pop up indicators ,total coordination with legrand mccb and mcb ranges
- Complete range of accessories: auxiliary contacts(NO+NC), rotary handles, sealable terminal shields IP30

The product's benefits

Usage

- Application on manage of loads (normal/emergency), motor earthing and phase inversion, ensure continuity of electrical system.

Avantages

- Full integrated with XL³ & XL³S

Documentation

TECHNICAL DOCUMENTATION

F04092EN-00_DSX_TSE_DIN.pdf | PDF (1.68Mo)

LE13538AB.pdf | PDF (2.85Mo)

CAD & Design specs / BIM

424109.dwg | DWG (0.13Mo)

CATALOGUE PAGE & OTHERS

ex223001_0236.pdf | PDF (0.1Mo)

ex223001_0240.pdf | PDF (0.09Mo)

Agreements & Certificates

LGRP-01381-V01.01-EN.pdf | PDF (0.89Mo)