

Product sheet



URA ONE LEGRAND

Emergency lighting luminaire URA ONE Non Permanent 350lm 1h Autotest IP42 IK07

REF. 660624 | EAN. 3414971994478

[> Visit e-catalogue](#)

Product characteristics

- Indoor IP42, IK07, with opal diffuser, high luminosity LEDs with optimized light distribution, LED lifetime around 150,000 hours
- For direct surface - mounting installation or flush-mounting installation in false ceilings with accessory ref. 661650 (white finish) or ref. 661651 (alu finish) , also with decorative frame, evacuation label vertical holder, flag - mounting or suspension with dedicated Accessories, including a special flush-mounting frame for URA ONE installation in C3 flush-mounting cutout
- Automatic connection terminal blocks for power supply and for rest mode wires with wiring capacity of 2x2,5 mm², with protection against hazardous connection to 230V
- Power supply: 230 V +/- 10% - 50/60 Hz. Ni-Cd or Ni-MH battery.
- 4 cable entries: 1 rectangular opening on the back and 3 knock-out entries diameter 20 mm, 1 on each side and 1 on upper side.

Recommendation / Restriction

- Indoor use only

Documentation

TECHNICAL DOCUMENTATION

The product's benefits

Installation

- Translucide back with knock-out honeycom structure to ease the choice of fixing holes especially when replacing an old luminaire. Horizontal and vertical levels adjustments.

Usage

- This luminaire is periodically tested with a weekly emergency lamp test and with a 3 monthly emergency duration test in order to check its operation. The green and amber LEDs are off during the emergency tests.


Avantages

- All installation modes are possible:- surface mounting with or without decorative frame- flush-mounting in false ceilings, with or without evacuation label vertical plate- flag-mounting or suspension with relating accessories
- Green and amber signaling LEDs for luminaire operating status indication
- Possible substitution of C3 fluorescent luminaire, with using flush-mounting frame ref. 661652, especially designed to recover C3 flush-mounted cutout.

CATALOGUE PAGE & OTHERS

→ LE12121AA.pdf | PDF (1.02Mo)


 S000083576FR-3.pdf | PDF (3.97Mo)

 S000083576EN_3.pdf | PDF (4.07Mo)

Agreements & Certificates


 AENOR S-007/000004 | (0.91Mo)

 AENOR-007/001689 | (0.9Mo)

 OC / CB-ES1842-M2-AENOR | (0.41Mo)

 ENEC-ENEC/000994 | (0.48Mo)

 ex223001_0907.pdf | PDF (0.06Mo)

 LG-660624.zip | ZIP

 ex223001_0906.pdf | PDF (0.09Mo)