

Product sheet



LEGRAND

Fuse carrier 3P for industrial cylindrical cartridge fuse
10 x 38 mm

REF. 005838 | EAN. 3245060058388

> [Visit e-catalogue](#)

Product characteristics


- With insulated carrier class II, padlockable with Accessory 005799
- Terminals capacity 1 x 25 mm² maxi, IP 2X, screw head PZ2
- Conforms to IEC standards 60269 - 1, 60269 - 2, 60269 - 2 - 1 and standard NF C 63 - 210
- Possibility to signal indicator blown fuse with accessory 005790
- Fuse not supplied

Recommendation / Restriction

- This product should be installed in compliance with installation rules, preferably by a qualified electrician. Incorrect installation and/or incorrect use can lead to risk of electric shock or fire. Before carrying out the installation, read the instructions and take account of the product's specific mounting location. Do not open up, dismantle, alter or modify the device except where specifically required to do so by the instructions. All Legrand products must be opened and repaired exclusively by personnel trained and approved by Legrand. Any unauthorised opening or repair completely cancels all liabilities and the rights to replacement and guarantees. Use only Legrand brand accessories.

Documentation

TECHNICAL DOCUMENTATION

 FA222CEN_03.pdf | PDF (0.8Mo)

 FA222C_03.pdf | PDF (0.76Mo)

CAD & Design specs / BIM

 005838.dwg | DWG (0.08Mo)

The product's benefits

Installation

- Fitted with two DIN rail clamps, one top side and one bottom side, allowing an independent removal of this product when the prong busbar supplying the row is still in place.

Usage

- Fitted with a label holder allowing a clear, visible and convenient identification of the circuit.

CATALOGUE PAGE & OTHERS

 ex223001_0092.pdf | PDF (0.23Mo)

Agreements & Certificates

 LGRP-2015-149-V1-EN.pdf | PDF (0.62Mo)

