

Product sheet



LEGRAND

Single phase current transformer (CT) for 84 x 34 mm bar - transformation ratio 1250/5

REF. 412142 | EAN. 3414970593375

> [Visit e-catalogue](#)

Product characteristics

- Current transformers (CT)
- Single-phase solid core current transformers - Used with ammeters, electricity meters or multi-function measuring units - Current at the secondary : 5 A - Can be fixed on plate, EN 60715 rail Cat.No 4 121 01/02/03/04/05/06/07, or bars - Secondary connected by terminals or lugs - Precision class : 1 % For 84 x 34 mm bar - Transformation ratio : 1250/5 - Output : 12 VA

Documentation

TECHNICAL DOCUMENTATION

-  F01960FR-03.pdf | PDF (0.77Mo)
-  Guide Technique : EMDX³ transformateurs de courant | PDF (2.96Mo)
-  F01960EN-02.pdf | PDF (0.8Mo)
-  Technical Guide: EMDX³ current transformers | PDF (2.98Mo)

CATALOGUE PAGE & OTHERS

-  ex223001_0127.pdf | PDF (0.07Mo)
-  ex223001_0128.pdf | PDF (0.07Mo)